

Filter Service Sp. z o.o.
ul. Sadowa 7a
95-100 Zgierz

Tel/Fax: (+48 42) 716 15 18
Tel/Fax: (+48 42) 717 15 81
Fax: (+48 42) 717 15 15
Fax: (+48 42) 715 44 33
Email: filter@filter-service.eu
www.filter-service.eu

Filtering half mask

FS-58V FFP3 NR D

Certificate

UE/127/2019/1437

Date of issue

06/05/2019

Standard

EN 149:2001 + A1:2009

Protection class

Class P3



Certification body:

CIOP-PIB 1437
Central Institute for Labour
Protection – National
Research Institute

Supervising body:

CIOP-PIB 1437*
Central Institute for Labour
Protection – National
Research Institute



Intended use

For protecting the user's respiratory tract against the harmful impact of air pollution in the form of solid and/or liquid particles forming aerosol (dust, fumes, mists) up to 30 × TLV.

Application

High concentration of respirable dusts; use when welding or soldering; the half mask protects against dusts containing beryllium, antimony, arsenic, cadmium, cobalt, nickel, radium, strychnine, and radioactive particles.

Specification



Half mask face-piece:

- Needle-punched nonwoven polyester
- Melt-blown nonwoven polypropylene
- Protective nonwoven

Additional elements:

- Exhalation valve
- Nosepiece for better facial fit within the nose area
- Polyethylene foam nose seal
- Head band pins for length adjustment
- Head band

Compact, face-fitting shape, pleasant-to-touch and delicate material. The half mask is covered with a special protective nonwoven layer, which prolongs its life. With the valve placed at the side of the half mask, it can be folded and put into a pocket without damaging it.

| | | | |
|---|-----------------------------|---|--|
| Filtering half mask | | | |
| FS-58V FFP3 NR D | | | |
| Certificate UE/127/2019/1437 | Date of issue 06/05/2019 | Standard EN 149:2001 + A1:2009 | Protection class Class P3  |
| Certification body: CIOP-PIB 1437 Central Institute for Labour Protection – National Research Institute | |  | |
| Supervising body: CIOP-PIB 1437* Central Institute for Labour Protection – National Research Institute | | | |

Requirements

The half mask meets the latest requirements:

Regulation (EU) 2016/425 of the European Parliament and of the Council of 9 March 2016 on personal protective equipment and repealing Council Directive 89/686/EEC.

Contraindications

The half mask must not be used under low-oxygen conditions (below 17%), which means that it is forbidden to use it in confined spaces, such as canals, manhole shafts, tanks. Also, the half mask does not protect against vapours and gases that are harmful for health and pose a life hazard. Do not use while extinguishing fire. The half mask does not supply oxygen. The half mask will not provide adequate facial fit for people with unshaved or bearded face.

Primary packaging: 15 pcs per box

Collective packaging: 360 pcs per carton

*This number is on the product after the CE mark