

Filter Service Sp. z o.o.  
ul. Sadowa 7a  
95-100 Zgierz, Poland

tel./fax: (+48 42) 716 15 18  
tel./fax: (+48 42) 717 15 81  
fax: (+48 42) 717 15 15  
fax: (+48 42) 715 44 33  
e-mail: [filter@filter-service.eu](mailto:filter@filter-service.eu)  
[www.filter-service.eu](http://www.filter-service.eu)

Filtering half-mask

## FS-930V FFP3 NR D

Certificate

UE/952/2024/1437  
Edition 1

Date of issue

30.01.2024

Reference standard

EN 149:2001 + A1:2009

Protection class

P3



Certification body:

CIOP-PIB 1437  
CIOP-BIP (Central Institute for  
Labour Protection — National  
Research Institute)

Supervision:

CIOP-PIB 1437\*  
CIOP-BIP (Central Institute for  
Labour Protection — National  
Research Institute)



## Intended use

Protection of human airways against harmful airborne solid particulates and/or liquids in aerosols (dust, smoke and mist) at a maximum exposure level of 30 times NDS (Polish Permissible Exposure Limit).

## Use

Exposure to high concentrations of respirable particulates; use when welding or soldering. Protection against particulates loaded with beryllium, antimony, arsenic, cadmium, cobalt, nickel, radium, strychnine, and radioactive solids.

## Specifications:

Half-mask dome:

- Polyester needled cloth
- Melt blown polypropylene non-woven cloth
- Outer coating needled cloth

Features:

- Exhaust valve
- Adjustable nose clip for a tight fit around the nose
- Polyethylene foam nose seal
- Head strap with fasteners for length adjustment
- Head straps

The automatic and optimized production process is key to the competitive pricing of the 900 series filtering half-masks.

A budget-friendly alternative to commercially available disposable respirators

without any compromise to the high quality and performance.

Filtering half-mask			
<b>FS-930V FFP3 NR D</b>			
Certificate UE/952/2024/1437 Edition 1	Date of issue 30.01.2024	Reference standard EN 149:2001 + A1:2009	Protection class P3 
Certification body: CIOP-PIB 1437 CIOP-BIP (Central Institute for Labour Protection — National Research Institute)			
Supervision: CIOP-PIB 1437* CIOP-BIP (Central Institute for Labour Protection — National Research Institute)			

## Reference requirements

The half-mask complies with the latest requirements of:

**Regulation (EU) 2016/425 of the European Parliament and of the Council of 9 March 2016 on personal protective equipment** and repealing Council Directive 89/686/EEC.

## Contraindications

Do not use in oxygen-deficient atmospheres ( $O_2 < 17\%$ ); use inside confined spaces, including ducts, chambers, vaults, or tanks is prohibited. The half-mask does not protect against pollutants formed by harmful or lethal gases and vapours. Do not use when extinguishing fire. The half-mask is not a contained oxygen-supplying respirator. The seal is insufficient on a face with stubble or longer hair. The half-mask does not protect the respiratory system against radioactive and carcinogenic particles, or microorganisms (bacteria, viruses, fungi and their derivatives), or enzymes.

Direct packaging: 10 pcs. in film bag

Bulk container: 500 pcs./cardboard box

\*See the product for the number which follows the CE marking.